

# SPARE PARTS LIST - ORDER

## CUSTOMER INFORMATION

Company name: \_\_\_\_\_

Shipping address: \_\_\_\_\_

Contact person: \_\_\_\_\_

## TO BE COMPLETED BY EASYMETAL

Date: \_\_\_\_\_

Person in charge: \_\_\_\_\_

Note: \_\_\_\_\_

Please tick the desired article and indicate the desired number of pieces behind it. (for example  2 )

### MAINTENANCE SETS:

401133 Maintenance refill 60/120/150 \_\_\_\_\_

401134 Maintenance refill 240/300 \_\_\_\_\_

401135 Maintenance refill 480/600 \_\_\_\_\_

401130 Basic maintenance for 60/120/150 \_\_\_\_\_

401131 Basic maintenance for 240/300 \_\_\_\_\_

401132 Basic maintenance for 480/600 \_\_\_\_\_

### FILTER AND CLEANING SOLUTION FOR MEMBRANES:

401201 Mem Clean Up 250 ml 60/120/150 \_\_\_\_\_

401202 Mem Clean Up 500 ml 240/300 (2 x for 480/600) \_\_\_\_\_

401229 Concentrate for preservation 250 ml \_\_\_\_\_

400534 Concentrate for preservation 500 ml \_\_\_\_\_

400532 Concentrate for preservation 1000 ml \_\_\_\_\_

400342 Wound thread filter 10" 1 micron \_\_\_\_\_

400349 Wound thread filter 20" 1 micron \_\_\_\_\_

400355 Carbon block 10" 1 micron \_\_\_\_\_

400348 Carbon block 20" 5 micron \_\_\_\_\_

401317 Carbon cartridge 10" \_\_\_\_\_

401318 Carbon cartridge 20" \_\_\_\_\_

400333 Softener cartridge 10" \_\_\_\_\_

400369 Softener cartridge 20" \_\_\_\_\_

### MEMBRANES:

401348 Membrane 3012-300 for 150/300/600 \_\_\_\_\_

401455 Membrane 3012-400 for 120/240/480 \_\_\_\_\_

400377 Membrane housing for TW3012 \_\_\_\_\_

### HOSES:

401294 Hose nature 10 mm (per m) \_\_\_\_\_

400201 Hose nature 6 mm (per m) \_\_\_\_\_

### GENERAL SPARE PARTS:

401148 Knurled cscrew 4 x 10 mm housing screw \_\_\_\_\_

400101 Ball valve 10 mm \_\_\_\_\_

400092 Screw-on connector 3/4" x 10 mm \_\_\_\_\_

401287 Seal ring for filter housing \_\_\_\_\_

400975 Solenoid valve mini 2 x 10 mm \_\_\_\_\_

400291 Pressure switch 1-10 bar \_\_\_\_\_

401105 Coupling for motor/pump \_\_\_\_\_

400929 Pump 500 L with bypass \_\_\_\_\_

401268 In-line butterfly valve \_\_\_\_\_

400833 Temperature probe Clickson 75° \_\_\_\_\_

400306 Solenoid valve input \_\_\_\_\_

### FITTINGS:

400150 Angle connector 10 mm \_\_\_\_\_

400153 Plug-in angle 10 mm \_\_\_\_\_

400144 Elbow 6 mm \_\_\_\_\_

400152 Plug-in angle 6 mm \_\_\_\_\_

400097 Bulkhead connector 10 mm \_\_\_\_\_

400188 Check valve 6 mm \_\_\_\_\_

400087 Plug connector inner thread 6 x 1/8 \_\_\_\_\_

400093 Screw-on connector 6 x 1/4 \_\_\_\_\_

400125 Angle screw connector 10 x 1/4 \_\_\_\_\_

400112 T-screw connector 10 x 3/8 \_\_\_\_\_

400113 T-screw connector 10 x 10 x 1/4 \_\_\_\_\_

400126 Angle screw connector 10 x 3/8 \_\_\_\_\_

400078 Screw connector 10 x 1/4 \_\_\_\_\_

400114 Y-connector 10 mm \_\_\_\_\_

400111 T-connector 10 mm \_\_\_\_\_

400187 Check valve 10 mm \_\_\_\_\_

400080 Screw-in connector 10 x 3/8 \_\_\_\_\_

400072 Screw-in socket 10 x 3/8 \_\_\_\_\_

400183 Plugs 10 mm \_\_\_\_\_

400139 Plug-in reducing connector 10 x 6 \_\_\_\_\_

400123 Straight connector 10 mm \_\_\_\_\_

## SPARE PARTS LIST - ORDER

Please tick the desired article and indicate the desired number of pieces behind it. (for example.    2   )

### TOOLS:

- Screwdriver allen key 2,5 + 4 mm for all screws \_\_\_\_\_
- Screwdriver electro \_\_\_\_\_
- Slot screwdriver No. 4 for adjusting the pump pressure \_\_\_\_\_
- Allen key 1,5 for adjusting the pressure switch \_\_\_\_\_
- 400909 Pipe cutter (important to cut tubes accurately and not squeeze) \_\_\_\_\_
- Water pump pliers \_\_\_\_\_
- 501367 Hose cutter
- 400199 Release aid fitting

These points provide a measuring instrument to control the pump pressure at the membrane.  
This is absolutely necessary during a membrane change or to check the system.

- 400397 Manometer 0-10 bar ¼" \_\_\_\_\_
- 400093 Screw-on connector 6 x ¼" \_\_\_\_\_
- 400139 Plug-in reducing connector 10 x 6 mm \_\_\_\_\_

---

Please sign your order and send it via e-mail or fax to easymetal

E-Mail: [office@easymetal.com](mailto:office@easymetal.com)

Fax: +43 2245 20123 45

Place and date: \_\_\_\_\_

Signature: \_\_\_\_\_